


## SL-LP 002 Zig Zag Writing Machine



### Product information

Load weight on the refill/pen, Make pen and writing paper face up to 60 and 90 tilt angle with a certain speed to write Z. Can test the refill, test bulk pen just replace the fixture can test 6 pcs or 10 pcs pens one time, with the function of automatic withdraw the test paper.

### Technical parameters

Paper movement Speed: adjustable 0-140 in/min revolutions per minute

Writing Plate Speed: Adjustable

1m/min -10m/min

Writing Angle 60° to 90°

Collet weight 50+/-0.5 grams

Refill Rotation In ON Condition - Refill rotation at 1-3 rpm

Marker Diameter : 35mm Max

Zig Zag/Holder Bar speed :1.375 inches Wide (1cycle=2.75inches)

Sample Size 6 Nos or 10 nos

Motor: Servo motor with programmable

Test paper: two rolls

Power: AC220V, 50HZ or 110V 60HZ